

SimSpray 3.x Tech Specs

Document version #1.10, Last updated: 2/7/24

Category		Description			
Weight	Unit Only:	145 lbs (w/o blaster) 158 lbs (w/ blaster)	66 kg (w/o blaster) 72 kg (w/ blaster)		
	Pallet Pack Container:	214 lbs (w/o blaster) 229 lbs (w/ blaster)	97 kg (w/o blaster) 104 kg (w/ blaster)		
Dimensions (W x D x H)	In Use:	51" x 25" x 81"	1.2954 x 0.635 x 2.0574 m		
	Closed:	24.5" x 25.25" x 48"	0.6223 x 0.6414 x 1.2192 m		
	Pallet Pack Container:	31" x 53" x 30"	0.7874 x 1.3462 x 0.762 m		
Working Space (Zone) Dimensions (W x D x H)	Ideal Open Space:	Minimum: 10' x 11' x 10'		Minimum: 3.048 x 3.3528 x 3.048 m	
		Minimum requirements include space for the SimSpray unit and for user movement.			
	<i>Note: Minimize reflections or infrared interference. SimSpray motion tracking uses infrared and photosensors. Aim SimSpray away from windows, TVs, infrared sources, and reflective materials. Cover sources of IR (Infrared) interference, turn off infrared emitting devices, and turn off nearby Bluetooth devices for best results. See the Positioning section of the Quick Start Guide</i>				
Power Requirements		Input Voltage	Input Frequency	Current	Misc.
	US	120 VAC	50-60Hz	2-5 Amps (In-Use: 2 Amps, Max: 5 Amps)	Standard, 3-pronged, bladed, household outlet
	INTL	100-250 VAC			Regional power plug adapter included
SimSpray Peripherals	VRSim Spray Gun, Powder Gun, and/or Abrasive Blasting Gun (infrared motion tracked) (supports 1 active user at a time)				
	VIVE Pro 2 (2448 x 2448 max resolution per eye, 90 Hz, 120° field of view), Valve Index (1440 x 1600 max res. per eye, 90 Hz), or similar HMD (infrared motion tracked first-person perspective video). (Mid-2023 and earlier units shipped with VIVE Pro (Eye).)				
	Touchscreen (touch interface and video) (1080p, 1920x1080 resolution, 60 Hz)				
	Speakers (sound)				
Required Connections	For Performance Portal score reporting, SimSpray requires an internet connection (wired preferred, WiFi available). If no internet connection is available, SimSpray may be switched to offline mode, but users will not be able to use the Performance Portal.				
Optional External Device Connections	HDMI AV to an additional external display (TV or Projector). SimSpray outputs 1080p (widescreen 1920x1080 resolution, progressive mode) at 60 Hz. <i>Additional external display and cabling not included but recommended if showing to 4+ people at the same time.</i>				
	USB flash drive. <i>Instructor USB included to collect SimSpray reports. Optionally, students and trainees may want their own USBs, not included. System supports 1 USB at a time. Use a non-SimSpray computer to email, print, make copies of, and/or delete reports.</i>				
Shipping Info	Indicate Section II of PI967 (Section II UN3481), hazard class 9 dangerous goods, lithium batteries (applies to SimSpray Enterprise units, which have 3 Guns). Each Gun (Paint, Powder, and/or Blast) contains a li-ion battery (3.85V, 740mAh, 13 grams, 1 cell * 2.84Wh).				
Tech Support Needs	Wired internet connection preferred, wireless available. <i>Ethernet cabling not included. Online connection recommended (starting in v3.3 and to support Curriculum Mode). Software updates and tech support may require an additional USB thumb drive and a non-SimSpray computer with access to the internet and access to download files (e.g. Dropbox).</i>				

Note: See Computer Tech Specs in a separate file. All specs are subject to change and may be replaced with comparable hardware or system.