

SimSpray Go Tech Specs

Document version #1.5, Last updated:5/11/22

Category		Description					
Weight		Unit Only:	37 lbs		16.78 kg		
Dimensions (W x D x H)		In Use:	33" x 23" x 29"		84 x 59 x 74 cm		
		Closed:	33" x 20" x 12"		84 x 51 x 31 cm		
		Shipping:	33" x 20" x 12"		84 x 51 x 31 cm		
Working Space (Zone) Dimensions (W x D x H)		Ideal Open Space:	Minimum: 10' x 9' x 9'			244 x 275 x 244 cm	
			SimSpray Go is designed to be used on desk or table. Minimum requirements include space for the SimSpray Go unit and for user movement. Admins can select trackable zones from default room shapes with small, medium, or large options (W x D):	S	6.7' x 6.7'	80 x 80 cm	
				M	15.7' x 12.5'	188 x 150 cm	
				L	25' x 12.5'	300 x 150 cm	
		Note: Minimize reflections or infrared interference. SimSpray uses a camera based tracking system. Cover sources of IR (Infrared) interference, turn off infrared emitting devices, or reposition or move the system.					
Power Requirements		Input Voltage	Input Frequency	Current	Misc.		
	US	120 VAC	50-60Hz	1.5-2 Amps (In-Use: 1.5 Amps, Max: 2 Amps)	Standard, 3-pronged, bladed, household outlet		
	INTL	100-250 VAC			Regional power plug adapter included		
SimSpray Peripherals		SimSpray Spray Gun (infrared motion tracked) (supports 1 active user at a time)					
		VIVE Pro Eye HMD (infrared motion tracked first-person perspective video) (2880 x 1600 resolution, 90 Hz, 110° field of view)					
		Speakers (sound from laptop)					
SimSpray System Laptop		Display: 15.6" HD Display (1920 x 1080)	Processor: Intel i7 10th Gen	Graphics: GeForce RTX 2060	Memory: 16 GB RAM	Operating System: Windows 10 Pro 64	
Required Connections		For Performance Portal score reporting, SimSpray requires an internet connection (wired preferred, WiFi available). If no internet connection is available, SimSpray may be switched to offline mode, but users will not be able to use the Performance Portal.					
Available External Device Connections		HDMI AV to an additional external display (TV or Projector). SimSpray outputs 1080p (widescreen 1920x1080 resolution, progressive mode) at 60 Hz. <i>Additional external display and cabling not included but recommended if showing to 4+ people at the same time.</i>					
		USB flash drive. <i>Instructor USB included to collect SimSpray reports. Optionally, students and trainees may want their own USBs, not included. System supports 1 USB inserted at a time. Use a non-SimSpray computer to distribute (email), print, make copies of, and/or delete reports.</i>					
Tech Support Needs		Wired internet connection preferred, wireless available. <i>Ethernet cabling not included. Online connection recommended (starting in v3.3 and to support Curriculum Mode). Software updates and tech support may require an additional USB and non-SimSpray computer with internet access and access to download files (e.g., Dropbox).</i>					

Note: Specs are subject to change and may be replaced with comparable hardware or system.